


New ACA RoQ analysis platform that revolutionize profile test practices



## HARDNESS APPLICATION |

Roll hardness is a key parameter defining a good roll.

**Identify problematic rolls** easily by mobile ACA RoQ hardness profiler and avoid runnability issues.

Embedded touch screen, Wi-Fi and built-in barcode reader allow instant hardness profile displayed and versatile data handling possibilities as well.

ACA RoQ analysis is not just a measure of roll quality, but also a great web quality tool.

Caliper variations are far too small to be picked up by online scanners or test labs. Hardness profile is an excellent indicator of paper or film material being level enough to be wound up.

## SPECIFICATIONS |



Display
Wireless Connectivity
Wired connection type
Batteries
Charging
Dimensions
Weight

Barcode Reader Max. Profile Resolution 4,3" touch screen
WLAN
USB
2 x Li-ion 2200 mAh
From USB port
180 x 80 x 122 mm
1,4 kg
Built-in camera

1 mm

ACA Systems Oy
Outilantie 3,
FIN-83750 Sotkuma, Finland
info@aca.fi
Tel. +358 13 569 911
Fax +358 13 569 949

www.aca.fi



